

## XBO HPN for digital cinema projection

Lampy ksenonowe krótkoślukowe

### Obszar zastosowań

- Cinema projection




### Cechy produktu

- Short arc with highest luminance for brighter screen illumination
- A lifetime of reliable performances with constant 6000 K color temperature
- Easy to maintain
- High level of arc stability
- Hot restart and instant light on screen
- Dimmable in a wide range




## Karta katalogowa rodziny produktów




---

333154\_XBO Xenon Short Arc Lamp



---

333156\_XBO Digital Xenon Short Arc Lamp



---

338611\_Xenon Short Arc Lamp

## Karta katalogowa rodziny produktów

### Dane techniczne

Opis produktu	Dane elektryczne		Wymiary i waga			
	Moc znamionowa	Zakres prądu zasilającego	Średnica	Długość	Długość bez trzonka pinowego/połączenie	Odległość a / LCL
XBO 1200 W/HPN OFR	1200,00 W	41...63 A	46,5 mm	345,0 mm	308,00 mm	144,0 mm <sup>1)</sup>
XBO 2000 W/HPN L OFR	2000,00 W	60...85 A	55,0 mm	345,0 mm	308,00 mm	144,0 mm <sup>1)</sup>
XBO 3000 W/HPN OFR	3000,00 W	77...108 A	55,0 mm	345,0 mm	308,00 mm	144,0 mm <sup>1)</sup>
XBO 3000 W/HPN L OFR	3000,00 W	75...103 A	60,0 mm	345,0 mm	308,00 mm	144,0 mm <sup>1)</sup>
XBO 4000 W/HPN OFR	4000,00 W	90...125 A	60,0 mm	345,0 mm	308,00 mm	144,0 mm <sup>1)</sup>
XBO 4000 W/HPN L OFR	4000,00 W	90...125 A	60,0 mm	345,0 mm	308,00 mm	144,0 mm <sup>1)</sup>
XBO 4000W/HPN XL OFR	4000,00 W	92...132 A	60,0 mm	345,0 mm	308,00 mm	144,0 mm <sup>1)</sup>
XBO 4500 W/HPN OFR	4500,00 W	108...150 A	60,0 mm	428,0 mm	389,00 mm	171,5 mm <sup>1)</sup>
XBO 4500 W/HPN L OFR	4500,00 W	108...150 A	60,0 mm	428,0 mm	389,00 mm	171,5 mm <sup>1)</sup>
XBO 6000 W/HPN OFR	6000,00 W	120...163 A	78,0 mm	428,0 mm	389,00 mm	171,5 mm <sup>1)</sup>
XBO 6000 W/HPN L OFR	6000,00 W	125...158 A	78,0 mm	428,0 mm	389,00 mm	171,5 mm <sup>1)</sup>
XBO 7000 W/HPN OFR	7000,00 W	135...175 A	78,0 mm	428,0 mm	389,00 mm	171,5 mm <sup>1)</sup>

Opis produktu	Długość przewodu od strony wejścia	Masa produktu	Długość przewodów	Odstęp między zimnymi elektrodami	Temperatury i warunki pracy
					Maks. dop. temp. otoczenia spłaszcza
XBO 1200 W/HPN OFR	235 mm	543,00 g	228,0	3,5 mm	230 °C
XBO 2000 W/HPN L OFR	235 mm	550,00 g	228,0	4,5 mm	230 °C
XBO 3000 W/HPN OFR	235 mm	601,00 g	228,0	4,5 mm	230 °C
XBO 3000 W/HPN L OFR	235 mm	659,00 g	228,0	5,0 mm	230 °C
XBO 4000 W/HPN OFR	235 mm	687,00 g	228,0	5,0 mm	230 °C
XBO 4000 W/HPN L OFR	235 mm	671,00 g	195,0	6,0 mm	230 °C
XBO 4000W/HPN XL OFR	235 mm	664,00 g	195,0	6.1 mm	230 °C
XBO 4500 W/HPN OFR	235 mm	880,00 g	228,0	6,0 mm	230 °C
XBO 4500 W/HPN L OFR	235 mm	880,00 g	228,0	6,0 mm	230 °C
XBO 6000 W/HPN OFR	235 mm	1050,00 g	228,0	7,5 mm	230 °C
XBO 6000 W/HPN L OFR	235 mm	1050,00 g	207,0	8,0 mm	230 °C
XBO 7000 W/HPN OFR	235 mm	1023,00 g	235,0	7,5 mm	230 °C

## Karta katalogowa rodziny produktów

Opis produktu	Trwałość		Dodatkowe dane produktu	
	Trwałość	Service Warranty Lifetime	Anoda (standardowe oznaczenie)	Katoda (standardowe oznaczenie)
XBO 1200 W/HPN OFR	3000 h	3500 h	SFaX30-9.5	SFa30-20
XBO 2000 W/HPN L OFR	3300 h	3500 h	SFaX30-9.5	SFa30-20
XBO 3000 W/HPN OFR	1500 h	1900 h	SFaX27-9.5	SFa27-20
XBO 3000 W/HPN L OFR	2200 h	2400 h	SFaX27-9.5	SFa27-20
XBO 4000 W/HPN OFR	650 h	750 h	SFaX27-9.5	SFa27-20
XBO 4000 W/HPN L OFR	1100 h	1400 h	SFaX27-9.5	SFa27-20
XBO 4000W/HPN XL OFR		2100 h	SFaX27-9.5	SFa27-20
XBO 4500 W/HPN OFR	1000 h	1300 h	SFaX30-9.5	SFa30-20
XBO 4500 W/HPN L OFR	1300 h	1500 h	SFaX30-9.5	SFa30-20
XBO 6000 W/HPN OFR	650 h	800 h	SFaX30-9.5	SFa30-20
XBO 6000 W/HPN L OFR	1000 h	1200 h	SFaX30-9.5	SFa30-20
XBO 7000 W/HPN OFR	400 h	500 h	SFaX30-9.5	SFa30-20

Opis produktu	Możliwości		Environmental information Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
	Chłodzenie	Dozwolona pozycja pracy	Date of Declaration	Primary Article Identifier
XBO 1200 W/HPN OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	18-02-2022	4008321741547   4062172030496
XBO 2000 W/HPN L OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	02-12-2022	4052899263437   4062172030458
XBO 3000 W/HPN OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	02-12-2022	4008321756602   4008321756589   4008321865502   4062172030328
XBO 3000 W/HPN L OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	02-12-2022	4052899301528   4062172030533
XBO 4000 W/HPN OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	02-12-2022	4008321336774   4052899091931   4062172030267
XBO 4000 W/HPN L OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	09-12-2022	4008321756640   4008321865533   4052899134829   4062172030274
XBO 4000W/HPN XL OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	01-04-2022	4062172225489
XBO 4500 W/HPN OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	02-12-2022	4008321756664   4008321756657   4062172030557
XBO 4500 W/HPN L OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	02-12-2022	4052899343351   4062172030595
XBO 6000 W/HPN OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	02-12-2022	4052899136373   4062172030649
XBO 6000 W/HPN L OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	16-12-2022	4052899087071   4052899343412   4062172030687   4062172111171
XBO 7000 W/HPN OFR	Wymuszone	s 15 p 15 <sup>2)</sup>	02-12-2022	4062172031691

## Karta katalogowa rodziny produktów

Opis produktu	Candidate List Substance 1	CAS No. of substance 1	Safe Use Instruction	Declaration No. in SCIP database
XBO 1200 W/HPN OFR	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	9216bf4f-e70a-4162-b102-76c4b3b8a81a   FF4D17FA-1438-4BC2-A606-AF20217550D1
XBO 2000 W/HPN L OFR	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	4b8c3a0d-e347-4664-955c-0d693a373f8c
XBO 3000 W/HPN OFR	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	de6757a1-76fc-43b2-bab8-5e345c7e8aec     03daa791-d4cf-4aaa-a1a2-88c31129bca3
XBO 3000 W/HPN L OFR	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	1f032a80-9e5a-4431-a675-c7036e7ea79f
XBO 4000 W/HPN OFR	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	5436255a-a46f-47df-b92e-f2c1c0ea2701
XBO 4000 W/HPN L OFR	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	e5c6268f-8ad3-41af-947c-83cfc899656d   2dee931a-3b3e-4fe9-b78f-d30e98231bdd
XBO 4000W/HPN XL OFR				In work
XBO 4500 W/HPN OFR	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	1fc58cd4-2db4-4dc8-8828-714ce9b1d0e5
XBO 4500 W/HPN L OFR	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	bdc206bb-8ab4-47d6-a813-e35a5e1b2612

## Karta katalogowa rodziny produktów

Opis produktu	Candidate List Substance 1	CAS No. of substance 1	Safe Use Instruction	Declaration No. in SCIP database
XBO 6000 W/HPN OFR	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	dd124654-3cfe-4a72-80db-15b376f17bc1
XBO 6000 W/HPN L OFR	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	2c9d4d2e-189b-4cd8-8946-603008b0d3df
XBO 7000 W/HPN OFR	Lead	7439-92-1	The identification of the Candidate List substance is sufficient to allow safe use of the article.	3028d909-e4c3-4ea0-8a8b-a58e460e8446

<sup>1)</sup> Odległość od końca trzonka do czubka elektrody (na zimno)

<sup>2)</sup> Do pionowej pozycji pracy: anoda (+) u góry

## Karta katalogowa rodziny produktów

---

### Instrukcja bezpieczeństwa

Because of their high luminance, UV radiation and internal pressure in both the hot and cold state, XBO lamps may only be operated in enclosed lamp casings specially constructed for the purpose. Xenon lamps are highly explosive. When hot, xenon lamps can cause burn marks. They should only be handled when the lamp is at room temperature. Always use the protective jackets supplied when handling these lamps. When packing the lamps and when installing or removing the lamps without their protective jackets, always wear protective clothing (face shield with neck protector, protective jacket and lint-free, cut-resistant gloves). For more information see the relevant in-pack leaflets and operating instructions.

---

### Wskazówki dotyczące zastosowania

Więcej szczegółowych informacji dotyczących grafik i zastosowania znajduje się w karcie katalogowej produktu

---

### Oświadczenie

Zastrzega się możliwość zmian bez uprzedzenia. Błędy i ominięcia są możliwe. Należy zawsze upewnić się czy korzystasz z najnowszej wersji katalogu.